




Solidar **ELITE 4K**

Superior Clarity, Smoothest Transitions!

The Elite 4K is our premier lens. It has improved transitions between all visual zones, and patented point-file software to ensure the refraction on the inside of the lens is calculated to match the prescription perfectly.

The Elite 4K has achieved the remarkable goal of neutralizing, to the greatest extent possible, the 5 principal errors inherent in off-axis vision: spherical aberration, oblique astigmatism, distortion, coma, and curvature of field. The correction of these optical errors appears as complex surface topography that provides exceptional vision, making the Elite 4K as close to wearing a single vision lens as possible. It's everything your patients want in a progressive lens!



Design Characteristics

Corridor Length (CL)	7 / 9 / 11 mm and Variable
Near Reference Point (NP _y)	10 / 12 / 14 mm and Variable
Fitting Height	15 / 17 / 19 mm and Variable
Inset	0 - 4 mm
Decentration	up to 10 mm at max. dia. 80 mm
Default Wrap	5°
Default Tilt	7°
Back Vertex	13 mm
Customize	Yes
Wrap Support	Yes
Atorical Optimization	Yes
Frame Selection	Yes
Max. Diameter	80 mm
Addition	0.50 - 5.00 dpt.
Application	Universal

You Won't Believe Your Eyes!™

